

TECHSPEC® Sliding 2" x 3" Base Plate Slot



Stock #52-083 **20+ In Stock**

- 1 + S\$35^{.35}

ADD TO CART

Volume Pricing

Qty 1-9	S\$35.35 each
Qty 10+	S\$31.36 each
Need More?	Request Quote

Product Downloads

General

English **Type:**

Physical & Mechanical Properties

76.20 **Length (mm):**

50.80 **Width (mm):**

9.50 **Thickness (mm):**

Black Anodized Aluminum

Construction:

Number of Slots:

2

Regulatory Compliance

Compliant

RoHS 2015:

[View](#)

Certificate of Conformance:

Compliant

Reach 250:

Product Details

- Increase the Versatility of Existing Mounting Equipment
- Ideal for Direct Mounting to Standard Breadboards
- Counterbored 1/4-20 or M6 x 1.0 Holes/Slots

TECHSPEC® Slotted 2" x 3" Base Plates are versatile mounting surfaces for breadboard and optical rail applications. Three 6.4mm diameter counterbored holes, ideal for 1/4"-20 hardware, allow posts or post holders to be mounted directly and can also accommodate a variety of other optomechanical components. The plates are ideal for adding extra versatility and adjustment capability to a benchtop optical system. TECHSPEC® Slotted 2" x 3" Base Plates are available in standard sliding or side to side sliding configurations, allowing for adjustment along or perpendicular to the optical axis of the system.

Technical Information

