

[See all 11 Products in Family](#)

TECHSPEC® HP Series Expanded Kit



HP Series: All lenses pictured may not be included in the kit. See "Contents of Kit" specification for included lenses.



Stock #25-611 [CONTACT US](#)

- 1 + **\$4,990.⁰⁰**

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | \$4,990.00 each |
| Need More? | Request Quote |

Product Downloads

General

Series:
HP Series

Contents of Kit:

- 8mm HP Series: [86-569](#)
- 12mm HP Series: [86-570](#)
- 16mm HP Series: [86-571](#)
- 25mm HP Series: [86-572](#)
- 35mm HP Series: [86-573](#)
- 50mm HP Series: [86-574](#)

Optical Properties

Working Distance (mm):

8mm HP Series: 100 - ∞
 12mm HP Series: 100 - ∞
 16mm HP Series: 100 - ∞
 25mm HP Series: 150 - ∞
 35mm HP Series: 200 - ∞
 50mm HP Series: 200 - ∞

Aperture (f/#):

8mm HP Series: f/1.8 - f/16
 12mm HP Series: f/1.8 - f/16
 16mm HP Series: f/1.8 - f/16
 25mm HP Series: f/1.8 - f/22
 35mm HP Series: f/1.8 - f/16
 50mm HP Series: f/1.8 - f/16

Sensor

Maximum Sensor Format:

8mm HP Series: 1.1"
 12mm HP Series: 1.1"
 16mm HP Series: 1.1"
 25mm HP Series: 1.1"
 35mm HP Series: 1.1"
 50mm HP Series: 4/3"

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details


- 1.1", C-Mount Lens
- Up to 20 MegaPixels, 1.85µm Pixel Size Sensors
- High Performance (HP), C-Mount Lens for Machine Vision
- 6.5mm to 50mm Focal Length

TECHSPEC® HP Series Fixed Focal Length Lenses are designed for the harsh demands of [factory automation \(FA\)](#) and machine vision (M) applications. The 6.5mm, 8mm, 12mm, 16mm, 25mm, and 35mm lenses are compatible with 1" and 1.1" sensor formats, while the 50mm lens is compatible with up to 4/3" sensor formats. The f/1.8 and f/2.8 apertures provide increased light throughput and high resolution performance. TECHSPEC® HP Series Fixed Focal Length Lenses are C-Mount and feature a locking focus and iris rings to prevent unwanted adjustments, as well as a front filter thread for integrating standard optical filters. Call for OEM Quantity Pricing.

Edmund Optics has created a family of high performance optical designs (the HP Series family) and developed three customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the HP Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **HP Series:** Features locking cam focus and iris adjustment. This is the most adjustable version of these optical designs and is the typical high quality machine vision lens.
- **HPI Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- **HPi Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

Technical Information



| Dimensions | | | | |
|-------------------|--------|--------|-------------|--------------------------------------|
| Focal Length (mm) | A (mm) | B (mm) | C (mm) | Filter Thread |
| 8mm, 1.1" Format | 70.4 | 83.5 | 43.5 | M105 x 1 with required adapter #8 |
| 12mm, 1.1" Format | 48 | 70.1 | 43.5 | M62 x 0.75 with required adapter 236 |
| 16mm, 1" Format | 48 | 60.4 | 57.3 - 59.5 | M46 x 0.75 |
| 25mm, 1" Format | 37.5 | 45.3 | 45.3 | M34 x 0.5 |
| 35mm, 1.1" Format | 48.1 | 65.8 | 60 - 66 | M37 x 0.75 |
| 50mm, 4/3" Format | 50 | 72.6 | 60.5 - 72.6 | M37.5 x 0.5 |