

[See all 1 Products in Family](#)

TECHSPEC® Unmounted Protected Gold Hollow Retroreflector



TECHSPEC® Unmounted Hollow Roof Retroreflectors

Stock **#17-547** **1 In Stock**

⊖ 1 ⊕ **\$623.00**

ADD TO CART

Volume Pricing	
Qty 1+	\$623.00 each
Need More?	Request Quote

Product Downloads

General

Retroreflector **Type:**

Physical & Mechanical Properties

90 **Clear Aperture (%):**

12.50 and 17.70 **Length of Legs (mm):**

90 ±10 arcsec **Accuracy (°):**

Optical Properties

Protected Gold **Coating:**

[Fused Silica](#) **Substrate:**

20-10 **Surface Quality:**

Coating Specification:
R_{avg} >96% @ 700 - 2000nm
R_{avg} >96% @ 2000 - 10,000nm

180 **Ray Deviation (°):**

700 - 10000 **Wavelength Range (nm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Ideal for Redirecting Light in One Axis
- Hollow Design Minimizes Dispersion
- Replaces Solid Roof or Porro Prisms in Optical Assemblies

TECHSPEC® Unmounted Hollow Roof Retroreflectors are constructed by cementing two coated prisms together to form a hollow roof. The hollow design enables these retroreflectors to be used over wide spectral ranges without loss due to dispersion or absorption. Incident light is reflected 180° back towards the source with great accuracy due to the 90° ± 10 arcsec roof tolerance. TECHSPEC Unmounted Hollow Roof Retroreflectors feature a 17.7 x 17.7mm footprint and can be mounted with [#17-242](#) and [#18-537](#). These retroreflectors are ideal for applications such as interferometry and optical delay lines.